

EX 3100 Print Server Powered by Fiery®

Achieve efficiency through automation with the EX 3100 Print Server for the Versant™ 3100 Press. Improve your bottom line with best-in-class processing, outstanding colour, time-saving workflow and variable data capabilities.



KEY BENEFITS OF THE EX 3100 PRINT SERVER

More consistent and accurate colour – The EX 3100 Print Server provides colour management tools that give operators easy control of colour quality and repeatability using Full Width Array technology for automated calibration and profiling. Fiery® Ultra Smooth Gradients combines 10-bit architecture and special processing to deliver stunning, smooth gradients that will delight your customers by printing with the true appearance designers intended.

More services income – The Fiery® server supports industry-leading variable data printing (VDP) formats such as PDF/VT, PPML, VPS, and VIPP® as well as exclusive Fiery® FreeForm™ technology

More finished jobs in less time – Fiery® Command WorkStation® centralises job management and provides an intuitive user interface to shorten setup times and automate common tasks to reduce errors.

More seamless integration – The EX 3100 Print Server integrates with technologies such as FreeFlow® Core, plus EFI™ MIS/ERP business software and other leading third-party prepress workflows. Fiery® JDF technology automates and integrates your business and print process to help you produce more jobs profitably.

EX 3100 Print Server Powered by Fiery®

HARDWARE/PLATFORM

- Fiery® FS200 Pro software
- Performance optimised by proprietary EFI™ hardware and software technology, including VX600 ASIC and Fiery® system software
- Server touchscreen interface for easy device management and status information with Fiery® QuickTouch software

FIERY® COLOUR TECHNOLOGY

- Fiery® Ultra Smooth Gradients
 - 1200x1200 dpi, 10-bit rendering resolution
- Ultra High Definition Resolution
- Automated colour calibration and profiling with Automated Colour Quality Suite (ACQS) and Full Width Array technology
- Object Oriented Halftones enable selection of different line screens for text, graphics and images
- Job-based calibration integration
- Fiery® Spot-On™ enables management of spot colour libraries and custom spot colour creation
- PANTONE® Approved
- Fiery® Color Profiler Suite creates, verifies and edits colour profiles
- Auto-detect Composite Overprint of grayscale, spot and CMYK colours for accurate representation of the designer's intent
- Fiery® Image Enhance Visual Editor
- Fiery® Graphic Arts Package, Premium Edition (option) provides expert tools for preflighting and troubleshooting jobs before printing
 - Intuitive curve editing and soft proofing with Fiery® ImageViewer
 - Control Bar Builder enables custom control bar creation in a visual interface

PRODUCTIVITY AND WORKFLOW

- Spool-RIP-Print simultaneously
- Adobe® PDF Print Engine (APPE) version 3¹
- Fiery® Command WorkStation®
- Fiery® Paper Catalog integration with the Versant™ 3100 Press Stock Library Manager running on the Fiery® server
- Advanced Job Management features such as Schedule Print, Suspend on Mismatch, Job Reorder, Rush Print, Proof Print and Quick Doc Merge
- Sequential Print
- Fiery® Hot Folders for PC and Mac
- Virtual Printers automates job preparation
- Support of PDF XObjects on a per-job basis

DOCUMENT PREPARATION

- Standard support for 330 x 660 mm media
- Set Page Device mapping
- Booklet Maker allows flawless booklet imposition from the Fiery® Driver
- Fiery® Impose-Compose offers visual document makeready and imposition
- User-Defined Finish Size for increased control over imposition settings
- Mixed Subset Finishing
- Enhanced support for offline finishing with slip sheet, job cover page, and offset by sheets, copies or sets

VARIABLE DATA PRINTING (VDP)

- Fiery® VDP Imposition
- Define Record Length
- VDP Resource Manager
- Supports the following formats:
 - FreeFlow® VI Compose, VIPP®
 - PPML 2.0/2.2/3.0
 - PDF/VT-1 and PDF/VT-2
 - Fiery® FreeForm™
 - Creo® VPS
- VDP Multi-Up Booklet

SECURITY FEATURES

- IP Filtering for IPv4/IPv6
- Secure Erase
- Backup and Restore
- Fiery® System Restore
- User Authentication via LDAP
- IP Sec Support
- SSL/TLS support
- Certificate Management
- Encryption of critical information

STANDARD CONFIGURATION

- Fiery® NX Station GL: Fiery® work stand, Fiery® Ticker, 22" monitor, wireless keyboard and mouse
- Fiery® Impose-Compose
- Fiery® Color Profiler Suite including EFI™ ES-2000 Spectrophotometer

FIERY® OPTIONS

- Fiery® Graphic Arts Package, Premium Edition
- Hard Drive Security Option
- Additional Fiery® Impose licenses
- Additional Fiery® Compose licenses

INTEGRATION^{*2}

- FreeFlow® Core
- Build unique apps and tools for your business with Fiery® API
- Native Fiery® JDF integrates creative, production and management information solutions, making digital production faster and more efficient
 - AGFA®: APOGEE™ Prepress, Kodak® Prinergy™ Workflow, Heidelberg Prinect
 - EFI™ MIS and Web-to-Print solutions, including EFI™ Digital StoreFront®

*1: Updated with enhancements and service releases on an ongoing basis
*2: Please contact your local Fuji Xerox representative for availability.

Print Server [EX 3100 Print Server Powered by Fiery®]

Item	Description
Type	External
CPU	Intel® Core™ i5-4570S Processor 2.9 up to 3.6 GHz with Turbo, Quad Core
Storage device	Hard disk: 1 TB, DVD-RW drive
Memory capacity	4 GB (Max: 4 GB)
Server Operation System	Windows® 10 IoT Enterprise (64bit)
Page Description Language	Adobe® PostScript® Level 1, 2 Adobe® PostScript® 3™
Print Data Format	PDF/X-1a, 3 and 4 ¹ Adobe® Acrobat® XI: Native PDF 1.3, 1.4, 1.5, 1.6, 1.7 CT/LW ¹ , EPS, TIFF, TIFF/IT-P1, DCS2.0 ¹ , JPEG ¹ , ExportPS ¹ , PDF2Go ¹ , PCL
Supported Operating System	Windows® 10 (32bit), Windows® 10 (64bit) Windows® 8.1 (32bit), Windows® 8.1 (64bit) Windows® 7 (32bit), Windows® 7 (64bit) Windows Server® 2016 (64bit), Windows Server® 2012 R2 (64bit) Windows Server® 2012 (64bit), Windows Server® 2008 R2 (64bit) Windows Server® 2008 (32bit), Windows Server® 2008 (64bit)

Item	Description
Supported Operating System	macOS 10.13 High Sierra, macOS 10.12 Sierra OS X 10.11 El Capitan, OS X 10.10 Yosemite, OS X 10.9 Mavericks OS X 10.8 Mountain Lion, Mac OS X 10.7 Lion
Interface	Ethernet: 1000BASE-T / 100BASE-TX / 10BASE-T USB: USB3.0 x 7, USB2.0 x 2
Network Protocol	JMF (JDF job messaging format), TCP/IP, IPP, LPR/LPD, Port 9100, SMB print sharing (over TCP/IP), FTP printing, Print via Email, Bonjour, SNMP v3, Point and Print (PnP)
Power Supply	AC100-240 V +/- 10 %, 6 A (100 V) / 3 A (240 V), 50/60 Hz common
Maximum Power Consumption	0.4 kW
Dimensions	Print Server : W 235 x D 464 x H 528 mm NX Station GL : W 800 x D 866 x H 1665 mm
Weight	Print Server : 17 kg NX Station GL : 45 kg

*1: Only available with Fiery® Graphic Arts Package, Premium Edition.

All product names and company names mentioned in this brochure are trademarks or registered trademarks of their respective companies. The product specifications, appearance and other details in this brochure are subject to change without notice for improvements.

For more information or detailed product specification, please call or visit us at

Fuji Xerox Asia Pacific Pte Ltd, Malaysia Operations 199202000004 (993478-A)



Head Office:

GF, 1F & 3F, Axis Business Park, Block C, No. 10, Jalan Bersatu 13/4, 46200 Petaling Jaya.
Tel: 03-7882 2888 Fax: 03-7882 2828 Hunting Line: 1-300-88-5880

Branches:

Penang: No. 3-G, 3-1 & 3-2, Persiaran Bayan Indah, Bayan Bay, 11900 Bayan Lepas Penang.
Tel: 04-643 5000 Fax: 04-644 4677

Johor Bahru: No.21 & 23, Jalan Setia Tropika 1/28, Taman Setia Tropika, 81200 Kempas, Johor Bahru.
Tel: 07-238 7868 Fax: 07-238 2678

Melaka: No.17, Jalan KL3/11, Kota Laksamana, 75200 Melaka.
Tel: 06-281 0466 Fax: 06-281 0408

Kota Kinabalu: Block K, Lot 65, Ground-5th Floor, KK Time Square, 88100 Kota Kinabalu, Sabah.
Tel: 088-486 888 Fax: 088-486 668

Kuching: 199A-201, Lot 3049 & 3050, Eastmoore Centre, 2 1/2 Mile Jalan Rock, 93200 Kuching, Sarawak.
Tel: 082-240 633, 082-254 633 Fax: 082-418 733

<https://www.fujixerox.com.my/>