

# GX Print Server 2 for the Versant™ 3100 Press

Tough, dependable print server for professional printing

## SUPERB SPEED AND IMAGE QUALITY

This print server is ideal for corporate offices and quick-print environments as well as professional printing in which quality and speed are needed to satisfy a wide range of requirements. GX Print Server 2 is powered by Fuji Xerox patented technology to deliver high resolution at high speed and features APPE (Adobe® PDF Print Engine) and CPSI (Configurable PostScript® Interpreter), 1200 x 1200 dpi resolution, 10-bit colour and straightforward spot colour management.

The developed architecture produces an intermediate data format that reduces RIP load while a RIP Accelerator Board maintains image quality through high-speed, lossless compression. In addition, fast serial transmission accelerates processing of heavy image data.

Also included is Full Width Array technology featuring automated colour calibration and profiling, digital smoothing technology for sharper text and lines, and 3D Calibration for highly precise colour management.

## VDP SUPPORT FOR EXPANDING PRINTING SERVICES

Improve the competitiveness of your business by offering variable data printing (VDP) capability. GX Print Server 2 for the Versant™ 3100 Press is fully compatible with PPML, and PDF/VT open-standard VDP formats as well as scalable turnkey products FreeFlow® VI Compose, VIPP®.

## REALISES SMOOTHER GRADATION CORRECTION

The gradation realised by 10-bit rendering is expressed smoother. Additionally, the gradation correction function results in excellent gradation for more natural, smoother reproduction.

## EASY, INTUITIVE USER INTERFACE

The user interface ensures fast, easy job setup and operation for any user. Printer functions, job status, error messages and other vital information can be seen at a glance on the print server display. The end result is smoother operation better accuracy.

## SEAMLESS INTEGRATION WITH A VARIETY OF TECHNOLOGIES

GX Print Server 2 for the Versant™ 3100 Press provides an excellent collaborative platform to help expand your printing business. The combination with FreeFlow® Digital Workflow Collection automates and maximises your workflow to deliver more job at a shorter turnaround.



# GX Print Server 2 for the Versant™ 3100 Press

## PLATFORM

- Model: A-SV07

## KEY FEATURES

- Print Station
  - Main UI software for GX Print Server 2
- JDF v1.2\*
  - Enables GX Print Server 2 integration with JDF workflow
- \*For software we support, please contact your local Fuji Xerox representative.
- APPE v3.9 / 4.7
  - Enables GX Print Server 2 to RIP and integrate with PDF workflow
- Color Profile Maker Pro (CPMP)
  - A colour management feature to create and adjust CMYK device link profiles
- Job Director - Imposer
  - An imposition layout feature easily operated from Print Station UI
  - Readymade template
- Job Director -Sequencer
  - A job editing feature with simple, visual UI

- PS Preflight
  - Checks errors or use of inappropriate font or colour
- Raster Image Viewer
  - Displays job preview to edit, adjust curve or brightness
- Warning / Detection
  - Prevent errors when using RGB, spot colour, total ink coverage, hairline and overprint.
- Logical Printer
  - Supports ability to create Hot Folders and logical printers
  - The hot folder relieves the user of the repetitive task of configuring print settings for multiple jobs and allows the direct printing of files without need for an application.
- Security
  - User password control
  - GX Print Server 2 security (log-in) protocol makes shared locations accessible only to authorised users

## STANDARD CONFIGURATION

- 23.8" display, keyboard and mouse
- i1Pro 2 Kit

## OPTIONS

- RIP Accelerator Board
- Ripped PDF Export Kit
- Stand for GX Print Server

## Print Server [GX Print Server 2 for the Versant™ 3100 Press]

Item	Description
Type	External
CPU	Intel® Xeon® Processor E3-1275v6 (3.8 GHz)
Storage device	Hard disk : 2 TB (System) + 2 TB x 3 (RAIDO), DVD Multi drive
Memory capacity	32 GB (Max : 32 GB)
Server Operation System	Windows® 10 IoT Enterprise (64bit)
Page Description Language	Adobe® PostScript® 3™, PPML, VIPP <sup>*1</sup>
Print Data Format	PS, PDF, EPS, TIFF, JPEG
Supported Operating System	Windows® 10 (32bit) Windows® 10 (64bit) Windows® 8.1 (32bit) Windows® 8.1 (64bit) Windows® 7 (32bit) [Service Pack 1] Windows® 7 (64bit) [Service Pack 1] Windows Server® 2016 (64bit) Windows Server® 2012 R2 (64bit) Windows Server® 2012 (64bit) Windows Server® 2008 R2 (64bit) [Service Pack 1] Windows Server® 2008 (32bit) [Service Pack 2] Windows Server® 2008 (64bit) [Service Pack 2]

Item	Description
Supported Operating System	macOS 10.13 High Sierra macOS 10.12 Sierra OS X 10.11 El Capitan OS X 10.10 Yosemite OS X 10.9 Mavericks Mac OS 9.2.2
Interface	Ethernet : 1000BASE-T / 100BASE-TX / 10BASE-T x 2 USB : USB3.0 x 6, USB2.0 x 2
Network Protocol	TCP/IP(lpd / FTP / IPP <sup>*2</sup> / SMB / JDF / HTTP), AppleTalk <sup>*3</sup> , Bonjour
Power Supply	AC100-240 V +/- 10 %, 3.8 A (100 V) / 1.6 A (240 V), 50/60 Hz common
Maximum Power Consumption	0.4 kW
Dimensions <sup>*4</sup>	W 190 x D 415 x H 365 mm
Weight <sup>*4</sup>	12.5 kg

\*1: Used with optional software FreeFlow® VI Compose.

\*2: Used to work with FreeFlow® Digital Workflow Collection.

\*3: AppleTalk is not supported by Mac OS X 10.6 Snow Leopard or later.

\*4: Print Server only.

PANTONE® and other Pantone trademarks are the property of Pantone LLC. All product names and company names mentioned in this brochure are trademarks or registered trademarks of their respective companies. The product specifications, appearance and other details in this brochure are subject to change without notice for improvements.



For more information or detailed product specification, please call or visit us at

Fuji Xerox Asia Pacific Pte Ltd, Malaysia Operations 199202000004 (993478-A)



### Head Office:

GF, 1F & 3F, Axis Business Park, Block C, No. 10, Jalan Bersatu 13/4, 46200 Petaling Jaya.  
Tel: 03-7882 2888 Fax: 03-7882 2828 Hunting Line: 1-300-88-5880

### Branches:

Penang: No. 3-G, 3-1 & 3-2, Persiaran Bayan Indah, Bayan Bay, 11900 Bayan Lepas Penang.  
Tel: 04-643 5000 Fax: 04-644 4677

Johor Bahru: No.21 & 23, Jalan Setia Tropika 1/28, Taman Setia Tropika, 81200 Kempas, Johor Bahru.  
Tel: 07-238 7868 Fax: 07-238 2678

Melaka: No.17, Jalan KL3/11, Kota Laksamana, 75200 Melaka.  
Tel: 06-281 0466 Fax: 06-281 0408

Kota Kinabalu: Block K, Lot 65, Ground-5th Floor, KK Time Square, 88100 Kota Kinabalu, Sabah.  
Tel: 088-486 888 Fax: 088-486 668

Kuching: 199A-201, Lot 3049 & 3050, Eastmoore Centre, 2 1/2 Mile Jalan Rock, 93200 Kuching, Sarawak.  
Tel: 082-240 633, 082-254 633 Fax: 082-418 733

<https://www.fujixerox.com.my/>